

Set axial
EAMM-A-X62-150A

Numar piesa: 8164657

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Turatie max.	5500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Cuplu transmisibil	47 Nm
Greutate produs	2340 g
Cod de interfata actuator	X62
Codul interfetei motor In	140A 150A
Nota privind materialele	Conform RoHS