

Protecție aerisire VABD-D3-L-GN12

Numar piesa: 8177961

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Presiune de lucru	0 MPa...1.2 MPa 0 bar...12 bar
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364 zona III
Tip de protectie	IP54
Temperatura ambianta	-50 °C...60 °C
Greutate produs	14 g
Tipul de montare	insurubabil cu filet exterior
Nota privind materialele	Conform RoHS
Material surub de aerisire	HP PA 12