

Cuplaj
EAMD-56-56-32-23X27-U
Numar piesa: 8196718

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	32 mm
Diametru de montare 2	23 mm
Dimensiune	56
Lungime nominala	56 mm
Pozitie de instalare	orice
Turatie max.	5500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	172 kgmm ²
Cuplu transmisibil	73 Nm
Greutate produs	435 g
Nota privind materialele	Conform RoHS