

# Unitate de ghidare FENG-32-125-GF

Numar piesa: 8204062

FESTO



## Fisa de date

| Caracteristica              | Valoare                                |
|-----------------------------|----------------------------------------|
| Dimensiune                  | 32                                     |
| Cursa                       | 125 mm                                 |
| Pozitie de instalare        | orice                                  |
| Ghidaj                      | Ghidaj de alunecare                    |
| Structura constructiva      | Ghidaj                                 |
| Protectie la explozie       | Respectati informatiile din certificat |
| Conformitatea LABS          | VDMA24364-B2-L                         |
| Temperatura ambianta        | -20 °C...80 °C                         |
| Fora de deplasare           | 30 N                                   |
| Masa in miscare             | 690.5 g                                |
| Greutate produs             | 1782.5 g                               |
| Tipul de montare            | cu filet interior                      |
| Nota privind materialele    | Conform RoHS                           |
| Material element de ghidare | otel aliaj inalt                       |
| Material carcasa            | Aliaj de aluminiu forjat, anodizat     |
| Material placa de jug       | Aliaj de aluminiu forjat, anodizat     |