


Set axial EAMM-A-C80-19-108C-S5

Numar piesa: 8216594

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	76.5 mm
Pozitie de instalare	orice
Raportul de transmisie	1:1
Turatie max.	6500 1/min
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 100 %
Tip de protectie	IP69K
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	34.8 kgmm ²
Cuplu transmisibil	21 Nm
Greutate produs	2650 g
Cod de interfata actuator	C80-19
Codul interfetei motor In	108C
Nota privind materialele	Conform RoHS