

Set axial EAMM-A-C80-19-138C-S5

Numar piesa: 8216595

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	87.5 mm
Pozitie de instalare	orice
Raportul de transmisie	1:1
Turatie max.	5500 1/min
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 100 %
Tip de protectie	IP69K
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	128 kgmm ²
Cuplu transmisibil	60 Nm
Greutate produs	3440 g
Cod de interfata actuator	C80-19
Codul interfetei motor In	138C
Nota privind materialele	Conform RoHS