

Set paralel EAMM-U-60-C42-6-68C-91-S5

Numar piesa: 8216596

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	60
Pozitie de instalare	orice
Raportul de transmisie	1:1
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 100 %
Tip de protectie	IP69K
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	27.6 kgmm ²
Cuplu transmisibil	3 Nm
Greutate produs	1640 g
Cod de interfata actuator	C42-6
Codul interfetei motor In	68C
Nota privind materialele	Conform RoHS