

Set paralel EAMM-U-60-C50-10-68C-91-S5

Numar piesa: 8216598

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	60
Pozitie de instalare	orice
Raportul de transmisie	1:1
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 100 %
Tip de protectie	IP69K
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	27.7 kgmm ²
Cuplu transmisibil	3 Nm
Greutate produs	1890 g
Cod de interfata actuator	C50-10
Codul interfetei motor In	68C
Nota privind materialele	Conform RoHS