

Set paralel EAMM-U-86-C50-10-88C-102-S5

Numar piesa: 8216599

FESTO



Fisa de date

| Caracteristica | Valoare |
|------------------------------|-----------------------|
| Dimensiune | 86 |
| Pozitie de instalare | orice |
| Raportul de transmisie | 1:1 |
| Conformitatea LABS | VDMA24364 zona III |
| Temperatura de depozitare | -25 °C...60 °C |
| Umiditate relativa | 0 - 100 % |
| Tip de protectie | IP69K |
| Temperatura ambianta | -10 °C...60 °C |
| Momentul de inertie al masei | 174 kgmm ² |
| Cuplu transmisibil | 9.5 Nm |
| Greutate produs | 2990 g |
| Cod de interfata actuator | C50-10 |
| Codul interfetei motor In | 88C |
| Nota privind materialele | Conform RoHS |