

Set paralel EAMM-U-86-C68-16-88C-102-S5

Numar piesa: 8216601

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	86
Pozitie de instalare	orice
Raportul de transmisie	1:1
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 100 %
Tip de protectie	IP69K
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	172.8 kgmm ²
Cuplu transmisibil	9.5 Nm
Greutate produs	4560 g
Cod de interfata actuator	C68-16
Codul interfetei motor In	88C
Nota privind materialele	Conform RoHS