

Set paralel EAMM-U-110-C68-16-108C-120-S5

Numar piesa: 8216602

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	110
Pozitie de instalare	orice
Raportul de transmisie	1:1
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 100 %
Tip de protectie	IP69K
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	794.1 kgmm ²
Cuplu transmisibil	25 Nm
Greutate produs	6180 g
Cod de interfata actuator	C68-16
Codul interfetei motor In	108C
Nota privind materialele	Conform RoHS