

Set paralel EAMM-U-110-C80-19-108C-120-S5

Numar piesa: 8216604

FESTO



Fisa de date

| Caracteristica | Valoare |
|------------------------------|-------------------------|
| Dimensiune | 110 |
| Pozitie de instalare | orice |
| Raportul de transmisie | 1:1 |
| Conformitatea LABS | VDMA24364 zona III |
| Temperatura de depozitare | -25 °C...60 °C |
| Umiditate relativa | 0 - 100 % |
| Tip de protectie | IP69K |
| Temperatura ambianta | -10 °C...60 °C |
| Momentul de inertie al masei | 794.1 kgmm ² |
| Cuplu transmisibil | 25 Nm |
| Greutate produs | 7200 g |
| Cod de interfata actuator | C80-19 |
| Codul interfetei motor In | 108C |
| Nota privind materialele | Conform RoHS |