

Kit paralel EAMM-U-87-T42-87A-147

Numar piesa: 8223783

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	87
Centru	147 mm
Pozitie de instalare	orice
Raportul de transmisie	1:1
Turatie max.	3000 1/min
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-20 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	0 °C...50 °C
Momentul de inertie al masei	41.2 kgmm ²
Cuplu de antrenare in gol	0.22 Nm
Cuplu transmisibil	3 Nm
Greutate produs	996 g
Cod de interfata actuator	T42
Codul interfetei motor In	87A
Nota privind materialele	Conform RoHS