

Cuplaj
EAMC-H-35-13-GB16-19
Numar piesa: 8228661

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	19 mm
Dimensiune	30/35
Lungime nominala	23.4 mm
Pozitie de instalare	orice
Turatie max.	8000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	5.8 kgmm ²
Cuplu transmisibil	15 Nm
Greutate produs	31 g
Nota privind materialele	Conform RoHS