

## Set axial EAMM-A-C50-10-79CB-S5

Numar piesa: 8230180

FESTO



### Fisa de date

| Caracteristica               | Valoare                |
|------------------------------|------------------------|
| Lungime nominala             | 57.7 mm                |
| Pozitie de instalare         | orice                  |
| Raportul de transmisie       | 1:1                    |
| Turatie max.                 | 8000 1/min             |
| Conformitatea LABS           | VDMA24364 zona III     |
| Temperatura de depozitare    | -25 °C...60 °C         |
| Umiditate relativa           | 0 - 100 %              |
| Tip de protectie             | IP69K                  |
| Temperatura ambianta         | -10 °C...60 °C         |
| Momentul de inertie al masei | 5.87 kgmm <sup>2</sup> |
| Cuplu transmisibil           | 12.5 Nm                |
| Greutate produs              | 890 g                  |
| Cod de interfata actuator    | C50-10                 |
| Codul interfetei motor In    | 79CB                   |
| Nota privind materialele     | Conform RoHS           |