

## Set axial EAMM-A-C50-10-114CA-S5

Numar piesa: 8230186

FESTO



### Fisa de date

Caracteristica	Valoare
Lungime nominala	74.7 mm
Pozitie de instalare	orice
Raportul de transmisie	1:1
Turatie max.	6500 1/min
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 100 %
Tip de protectie	IP69K
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	34.8 kgmm <sup>2</sup>
Cuplu transmisibil	17 Nm
Greutate produs	1980 g
Cod de interfata actuator	C50-10
Codul interfetei motor In	114CA
Nota privind materialele	Conform RoHS