


Set axial EAMM-A-C68-16-110CA-S5

Numar piesa: 8230189

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	88.2 mm
Pozitie de instalare	orice
Raportul de transmisie	1:1
Turatie max.	6500 1/min
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 100 %
Tip de protectie	IP69K
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	34.8 kgmm ²
Cuplu transmisibil	21 Nm
Greutate produs	2220 g
Cod de interfata actuator	C68-16
Codul interfetei motor In	110CA
Nota privind materialele	Conform RoHS