

# Suport lagar LN-160

Numar piesa: 9037

FESTO



## Fisa de date

| Caracteristica                       | Valoare   |
|--------------------------------------|---|
| Dimensiune                           | 160   |
| Pe baza standardului                 | ISO 15552 (anterior si VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Clasa de rezistenta la coroziune KBK | 1 - stres redus la coroziune  |
| Conformitatea LABS                   | VDMA24364-B2-L  |
| Temperatura ambianta                 | -40 °C...150 °C   |
| Greutate produs                      | 6234 g  |
| Nota privind materialele             | Conform RoHS  |
| Material fixare                      | Fonta ductila   |