

## Suport lagar LN-320

Numar piesa: 9040

**FESTO**



## Fisa de date

| Caracteristica                       | Valoare                                                               |
|--------------------------------------|-----------------------------------------------------------------------|
| Dimensiune                           | 320                                                                   |
| Pe baza standardului                 | ISO 15552 (anterior si VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Clasa de rezistenta la coroziune KBK | 1 - stres redus la coroziune                                          |
| Conformitatea LABS                   | VDMA24364-B2-L                                                        |
| Temperatura ambianta                 | -40 °C...150 °C                                                       |
| Greutate produs                      | 22404 g                                                               |
| Nota privind materialele             | Conform RoHS                                                          |
| Material fixare                      | Fonta ductila                                                         |