

Tub poli-stratificat PM-6

Numar piesa: 9087

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	8 mm
raza de indoire relevanta pentru debit	25 mm
Ø interior	5.2 mm
Presiune de lucru in functie de temperatura	-0.95 bar...30 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-29 °C...65 °C
Greutatea produsului in functie de lungime	0.032 kg/m
Culoare	negru
Nota privind materialele	Conform RoHS
Material furtun	Aliaj de aluminiu forjat PE