

Adaptor
AD-G1/8-1/8NPT-I
Numar piesa: 9395

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	5.95 mm
Presiune de functionare interval complet de temperatura	-0.95 bar...10 bar
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Cuplu de strangere max. conexiune pneumatica 1	6 Nm
Cuplu de strangere max. conexiune pneumatica 2	7 Nm
Cuplu de strangere nominal	10.55 Nm
Toleranta fata de cuplul de strangere nominal	± 20 %
Greutate produs	10.38 g
Conector pneumatic 1	Filet exterior G1/8
Conexiune pneumatica 2	Filet interior 1/8 NPT
Nota privind materialele	Conform RoHS
Material garnituri	PVC
Material carcasa	Otel galvanizat