

Adaptor AD-1/4NPT-G1/4-I

Numar piesa: 9625

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	7.95 mm
Presiune de functionare interval complet de temperatura	-0.95 bar...10 bar
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Cuplu de strangere max. conexiune pneumatica 1	12 Nm
Cuplu de strangere max. conexiune pneumatica 2	11 Nm
Greutate produs	21 g
Conector pneumatic 1	Filet exterior 1/4 NPT
Conexiune pneumatica 2	Filet interior G1/4
Nota privind materialele	Conform RoHS
Material garnituri	PVC
Material carcasa	Otel galvanizat