

Adaptor AD-3/8NPT-G3/8-I

Numar piesa: 9626

FESTO



Fisa de date

| Caracteristica | Valoare |
|---|------------------------------|
| Latimea nominala | 11.5 mm |
| Presiune de functionare interval complet de temperatura | -0.95 bar...10 bar |
| Clasa de rezistenta la coroziune KBK | 1 - stres redus la coroziune |
| Conformitatea LABS | VDMA24364-B1/B2-L |
| Temperatura ambianta | -10 °C...60 °C |
| Cuplu de strangere max. conexiune pneumatica 1 | 22 Nm |
| Cuplu de strangere max. conexiune pneumatica 2 | 25 Nm |
| Greutate produs | 25.98 g |
| Conector pneumatic 1 | Filet exterior 3/8 NPT |
| Conexiune pneumatica 2 | Filet interior G3/8 |
| Nota privind materialele | Conform RoHS |
| Material garnituri | PVC |
| Material carcasa | Otel galvanizat |