


Ventil de impuls VLK-3-PK-3

Numar piesa: 9639

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	2.5 mm
Presiune de lucru	2.5 bar...8 bar
Debit nominal standard (normalizat conform DIN 1343)	90 l/min
Protectie la explozie	Respectati informatiile din certificat Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	170 g
Tipul de montare	pe cadrul de montare
Material garnituri	TPE-U (PU)
Material carcasa	Zinc turnat sub presiune