


Supapa evacuare rapida SEU-1/2-NPT

Numar piesa: 9801

FESTO



Fisa de date

Caracteristica	Valoare
Functie de ventil	Exhaustare rapida
Selectare functie suplimentara	cu amortizor de zgomot
Conector pneumatic 1	1/2 NPT
Conexiune pneumatica 2	1/2 NPT
Tipul de montare	insurubabil
Debit nominal normal de aerisire 0,6->0,5 MPa (6->5 bari, 87->72,5 psi)	4020 l/min
Debit normal ventilare 0,6->0 MPa (6->0 bari, 87->0 psi)	6500 l/min
Debit nominal normal de ventilare 0,6->0,5 MPa (6->5 bari, 87->72,5 psi)	4560 l/min
Presiune de lucru	0.3 bar...10 bar
Temperatura ambianta	-20 °C...75 °C
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Latimea nominala	15 mm
Nota referitoare la mediul de lucru/comanda	Posibilitatea operarii cu ulei (necesar pentru operare ulterioara)
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-20 °C...75 °C
Nivel de presiune acustica	86 dB(A)
Nota privind materialele	Conform RoHS