



# Motorski vod NEBM-S1G9-E-15-LE6

Broj artikla: 550742

☆ Kernprogramm

odgovara za koračni motor EMMS-ST...

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Svojstvo kabla	prikladno za energetski lanac
Područje pogonskog napona DC	0 ... 72 V
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline kod pokretnog postepenja kablova	-40 ... 70 °C
Temperatura okoline	-40 ... 70 °C
Bending radius, flexible cable installation	≥ 58 mm
Electrical connection 1, function	Field device side
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, design	ugaono
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	6
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	7
Electrical connection 2, occupied pins/wires	6
Krajevi žica	Završetak žice
Struktura kabla	7x0,34 zaslonjeno
Prečnik kabla	8 mm
Dužina kabla	15 m
Nazivni presek provodnika	0,34 mm <sup>2</sup>
Cable identification	Without inscription label holder
Boja izolacije	sivo
Materijal - napomena	RoHS komfornost
Informacija o materijalu, plašt kabla	TPE-U(PUR)