


# Operatör paneli FED-1010

Ürün numarası: 543516

FESTO

Display and operator unit with LCD graphic display for connecting to PLC systems.

Products to be discontinued. Available until 2010.



## Bilgi sayfası

Özellik	Değer
Depth	91 mm
Yükseklik	232 mm
Uzunluk	287 mm
Max. front panel thickness	5 mm
User memory	32 Mbyte
Real-time clock	evet
Real-time clock deviation	130 s / month
Number of colours	64 k
Gösterge	TFT colour
Display property	Touchscreen
Display size	10,4"
Backup battery	3 V / 270 mA lityum
Operating voltage range DC	18 ... 30 V
Display resolution	VGA, 640x480 Pixel
Nominal çalışma gerilimi DC	24 V
Nominal çalışma gerilimindeki akım tüketimi	1,2 A
CE mark (see declaration of conformity)	to EU directive for EMC
Depolama sıcaklığı	-20 ... 70 °C
Relatif hava nemi	5 - 85 % yoğunlaşmayan
Koruma sınıfı	IP65 front, IP20 back
Çevre sıcaklığı	0 ... 45 °C
Müsaade edilebilirlik	C-Tick
Ürün ağırlığı	2.250 g
AUX interface	Sub-D 9-pinli Soket
Printer interface	RS232 Sub-D 15-pin Soket
PLC interface	RS232 Sub-D 15-pin Erkek soket
USB interface	evet
Ethernet arabirimi	RJ45 10/100 MBd 2nd Ethernet interface, optical 10 MBd
Bağlantı şekli	Ön panel montajı
Malzeme hakkında not	Conforms to RoHS
Certification according to NEC 500	Class I, Div.2, Gr. A,B,C,D