

Pipe and tubing cutters

FESTO




Pipe and tubing cutters

Technical data

FESTO

Tubing cutter PAN-VOS

for flame retardant PAN-V0 tubing
The integrated stop assures that the PVC sheath for PAN-V0 tubing is always cut to the correct length. The blade design prevents damage to the inner, polyamide tubing.



Dimensions and ordering data					
For tubing O.D. [mm]	D1 Ø [mm]	D2 Ø	D3 Ø	X	Part No. Type
6	6	8	4	17	160 554 PAN-VOS-6/8
8	8	10	6	18	
10	10	12	7.5	20	160 555 PAN-VOS-10/12
12	12	14	9	23	

Hose cutter PXS-B

for metal braided shielded hose



Ordering data		
	Part No.	Type
Hose cutter	11 572	PXS-B

Disconnecting pliers ZDS

with cutter, for removing plastic tubing PP-3, PU-3, PP-4, PU-4 from barbed nipples



Ordering data		
	Part No.	Type
for 3 mm tubing	9 090	ZDS-PK-3
for 4 mm tubing	9 522	ZDS-PK-4

Pipe and tubing cutters

Technical data

FESTO

Connecting pliers ZMS-PK-3/4

with cutter, for connecting plastic tubing PP-3, PU-3, PP-4, PU-4 to barbed nipples

ZDS-PK-4 is only suitable for single barbed fittings.



Ordering data		
	Part No.	Type
Connecting pliers	9 341	ZMS-PK-3/4

Pipe cutter ZR

The pipe cutter ZR is used for cutting PQ-PA plastic piping with outside diameters of up to 28 mm to length. It is not suitable for tubing with metal casing.



Ordering data		
	Part No.	Type
Pipe cutter	194 592	ZR

Pipe and tubing cutter ZRS

The pipe and tubing cutter ZRS is used for cutting plastic and nitrile rubber tubing with outer diameters of up to 20 mm, with or without textile insert. It is not suitable for tubing with metal casing. It also has an integrated safety catch to prevent unauthorised opening.



Ordering data		
	Part No.	Type
Pipe and tubing cutter with 2 spare blades	7 658	ZRS
10 spare blades for pipe and tubing cutter	218 606	ZRS 10-pack