

Push-in fittings QBM, Quick Basic, mini, inch

FESTO



Push-in fittings QBM, Quick Basic, mini, inch

FESTO

Technical data


General technical data		
Connecting thread	UNF	NPT
Size	Mini	
Design	Push-pull principle	
Mounting position	Any	
Type of seal on threaded plug	Sealing ring	Coating

Operating and environmental conditions		
Temperature-dependent operating pressure	[Psi]	-13.8 ... +145
Operating medium		Filtered compressed air, lubricated or unlubricated
		Vacuum
Ambient temperature	[°F]	32 ... 140
Corrosion resistance class	CRC ¹⁾	1

1) Corrosion resistance class 1 according to Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Materials

Sectional view



	QBM
1 Releasing ring	POM
2 Tubing seal	NBR
3 Housing	Nickel-plated brass
	PBT
4 Tube retaining claw	High-alloy stainless steel
Note on materials	Contains PWIS (paint wetting impairment substances)
	RoHS-compliant

Push-in fittings QBM, Quick Basic, mini, inch

Product range overview

Design	Version	Type	Connection D1			Connection D2			→ Page/ Internet
			UNF thread	NPT thread	Tubing O.D.	Push-in sleeve Ø	Tubing O.D.	Push-in sleeve Ø	
Straight design	Push-in fitting – Male thread with external hex								
		QBM	10-32	–	–	–	1/8, 5/32, 1/4	–	5
			–	1/8			1/8, 5/32, 1/4		
			–	1/4			1/8, 1/4		
	Push-in fitting – Male thread with internal hex								
		QBM-...-I	10-32	–	–	–	1/8, 5/32, 1/4	–	5
			–	1/8			1/4		
	Push-in fitting – Female thread with external hex								
		QBMF	10-32	–	–	–	1/8, 5/32, 1/4	–	6
	Push-in connector								
		QBM-...T	–	–	1/8	–	–	–	7
					5/32				
					1/4				
		QBM-...-T reducing	–	–	5/32	–	1/8	–	
3/16					1/8				
1/4					5/32				
Push-in connector with push-in sleeve									
	QBM-...H	–	–	–	5/32	1/8	–	7	
Blanking plug									
	QBMC-...H		–	–	1/8	–	–	8	
L-shape	Push-in L-fitting – Male thread with external hex								
		QBML	10-32	–	–	–	1/8, 5/32, 1/4	–	9
			–	1/8			1/8, 1/4		
			–	1/4			1/8, 1/4		
	Push-in long L-fitting – Male thread with external hex								
		QBMLL	10-32	–	–	–	1/8, 1/4	–	9
			–	1/8			1/8, 1/4		
	Push-in L-connector								
		QBML-...T	–	–	1/8	–	–	–	10
					5/32				
1/4									

Push-in fittings QBM, Quick Basic, mini, inch

Product range overview

FESTO

Design	Version	Type	Connection D1			Connection D2			→ Page/ Internet
			UNF thread	NPT thread	Tubing O.D.	Push-in sleeve Ø	Tubing O.D.	Push-in sleeve Ø	
T-shape	Push-in T-fitting – Male thread with external hex								
		QBMT	10-32	–	–	–	1/8, 5/32, 1/4	–	11
			–	1/8			1/8, 1/4		
			–	1/4			1/4		
	Push-in T-connector								
		QBMT-...T	–	–	1/8	–	–	–	12
					5/32				
					1/4				
		QBMT-...T reducing	–	–	5/32	–	1/8	–	
					1/4		5/32		
	Push-in T-fitting – Male thread with external hex								
		QBMTL	10-32	–	–	–	1/8, 5/32, 1/4	–	13
			–	1/8			1/8, 1/4		
			–	1/4			1/8		
Y-shape	Push-in Y-connector								
		QBMY-...T	–	–	1/8	–	–	–	14
					5/32				
					1/4				
		QBMY-...T reducing	–	–	5/32	–	1/8	–	
					1/4		5/32		


Push-in fittings QBM, Quick Basic, mini, inch

Technical data

Push-in fitting QBM

Male thread
with external hex


UNF thread



UNF

NPT


Dimensions and ordering data											
Connection	Nominal size	Tubing O.D.	D5 Ø	L1	L2	L3	⌀	Weight/piece	Part No.	Type	PU ¹⁾
D1	[inch]	D2						[oz]			
UNF thread											
10-32	0.079	1/8	7.2	16.4	3.6	12.8	5/16	0.071	533266	QBM-10-32-UNF-1/8-U	10
	0.098	5/32	8.0	16.9	3.6	13.3	5/16	0.106	572303	QBM-10-32-UNF-5/32-U	10
	0.098	1/4	10.5	18.9	3.6	15.3	7/16	0.353	573050	QBM-10-32-UNF-1/4-U	10
NPT thread											
1/8	0.098	1/8	7.2	17.5	8.5	13.4	7/16	0.212	533270	QBM-1/8-1/8-U	10
	0.118	5/32	8.0	17.9	8.5	13.8	7/16	0.317	572305	QBM-1/8-5/32-U	10
	0.197	1/4	10.5	19.5	8.5	15.4	7/16	0.635	573051	QBM-1/8-1/4-U	10
1/4	0.098	1/8	7.2	21.5	10.5	15.7	9/16	0.529	572306	QBM-1/4-1/8-U	10
	0.197	1/4	10.5	22.3	10.5	16.5	9/16	1.023	573052	QBM-1/4-1/4-U	10

1) Packaging unit

Push-in fitting QBM-...-I

Male thread
with internal hex


UNF thread



UNF

NPT

Dimensions and ordering data											
Connection	Nominal size	Tubing O.D.	D5 Ø	L1	L2	L3	⌀	Weight/piece	Part No.	Type	PU ¹⁾
D1	[inch]	D2						[oz]			
UNF thread											
10-32	0.094	1/8	7.0	16.4	3.6	–	3/32	0.071	572311	QBM-10-32-UNF-1/8-I-U	10
	0.094	5/32	8.0	17.0	3.6	–	3/32	0.106	572312	QBM-10-32-UNF-5/32-I-U	10
	0.094	1/4	10.5	19.0	3.6	–	3/32	0.423	573054	QBM-10-32-UNF-1/4-I-U	10
NPT thread											
1/8	0.157	1/4	10.5	19.5	8.5	15.4	3/32	0.635	573055	QBM-1/8-1/4-I-U	10


1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch

Technical data

FESTO

Push-in fitting QBMF




Dimensions and ordering data										
Connection	Nominal size	Tubing O.D.	D5 Ø	L1	L2	≅	Weight/piece [oz]	Part No.	Type	PU ¹⁾
D1	[inch]	D2								
UNF thread										
10-32	0.098	1/8	7.5	18.8	6.0	5/16	0.071	572282	QBMF-10-32-UNF-1/8-U	10
	0.118	5/32	8.0	19.2	6.0	5/16	0.176	572283	QBMF-10-32-UNF-5/32-U	10
	0.118	1/4	10.5	20.5	6.0	7/16	0.212	573066	QBMF-10-32-UNF-1/4-U	10

1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch

Technical data

Push-in connector QBM-...T




Dimensions and ordering data									
Tubing O.D. D1	Nominal size [inch]	Tubing O.D. D2	D4 Ø	D5 Ø	L1	Weight/piece [oz]	Part No.	Type	PU ¹⁾
1/8	0.094	–	–	7.5	23.6	0.035	572277	QBM-1/8T-U	10
5/32	0.118	–	–	8.4	24.5	0.071	572278	QBM-5/32T-U	10
1/4	0.197	–	–	11.2	28.6	0.106	573056	QBM-1/4T-U	10
Reducing									
5/32	0.094	1/8	7.5	8.4	24.1	0.071	572279	QBM-5/32T-1/8-U	10
3/16	0.098	–	7.5	11.5	28.7	0.106	573057	QBM-3/16T-1/8-U	10
1/4	0.138	5/32	8.8	11.2	28.1	0.106	573058	QBM-1/4T-5/32-U	10

1) Packaging unit

Push-in connector QBM-...H

with push-in sleeve



Dimensions and ordering data									
Push-in sleeve Ø D1	Nominal size [inch]	Tubing O.D. D2	D5 Ø	L1	L2	Weight/piece [oz]	Part No.	Type	PU ¹⁾
5/32	0.094	1/8	7.6	30.4	12.4	0.035	572280	QBM-5/32H-1/8-U	10


1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch

Technical data

FESTO

Blanking plug QBMC-...H



Dimensions and ordering data							
Push-in sleeve Ø D1	D2 Ø	L1	L2	Weight/piece [oz]	Part No.	Type	PU ¹⁾
1/8	5.0	20.0	18.0	0.035	572281	QBMC-1/8H-U	10


1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch

Technical data

Push-in L-fitting QBML

Male thread
with external hex




Dimensions and ordering data												
Connection	Nominal size	Tubing O.D.	D5 Ø	H1	H2	H3	L1	⌀	Weight/piece [oz]	Part No.	Type	PU ¹⁾
D1	[inch]	D2										
UNF thread												
10-32	0.098	1/8	7.6	15.3	3.6	–	13.5	5/16	0.071	533285	QBML-10-32-UNF-1/8-U	10
	0.098	5/32	8.7	15.9	3.6	–	14.6	5/16	0.176	572308	QBML-10-32-UNF-5/32-U	10
	0.098	1/4	11.3	17.2	3.6	–	16.1	5/16	0.353	573059	QBML-10-32-UNF-1/4-U	10
NPT thread												
1/8	0.098	1/8	7.6	15.8	8.5	11.7	13.5	7/16	0.176	533289	QBML-1/8-1/8-U	10
	0.118	1/4	11.3	17.7	8.5	13.6	16.1	7/16	0.564	573060	QBML-1/8-1/4-U	10
1/4	0.098	1/8	7.6	18.3	10.5	12.5	13.5	9/16	0.282	572310	QBML-1/4-1/8-U	10
	0.118	1/4	11.3	20.2	10.5	14.4	16.1	9/16	0.811	573061	QBML-1/4-1/4-U	10

1) Packaging unit

Push-in long L-fitting QBMLL

Male thread
with external hex



Dimensions and ordering data												
Connection	Nominal size	Tubing O.D.	D5 Ø	H1	H2	H3	L1	⌀	Weight/piece [oz]	Part No.	Type	PU ¹⁾
D1	[inch]	D2										
UNF thread												
10/32	0.098	1/8	7.6	23.9	3.6	–	13.5	5/16	0.282	572286	QBMLL-10-32-UNF-1/8-U	10
	0.098	1/4	11.3	28.7	3.6	–	16.1	5/16	0.317	573064	QBMLL-10-32-UNF-1/4-U	10
NPT thread												
1/8	0.098	1/8	7.6	24.4	8.5	20.3	13.5	7/16	0.388	572287	QBMLL-1/8-1/8-U	10
	0.118	1/4	11.3	32.7	8.5	28.6	16.1	7/16	0.494	573065	QBMLL-1/8-1/4-U	10


1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch

Technical data

FESTO

Push-in L-connector QBML-...T



Dimensions and ordering data									
Tubing O.D.	Nominal size	D5 Ø	D6 Ø	H1	H2	Weight/piece [oz]	Part No.	Type	PU ¹⁾
D1	[inch]								
1/8	0.094	7.5	3.2	13.5	5.4	0.071	572284	QBML-1/8T-U	10
5/32	0.118	8.4	3.2	14.5	5.8	0.106	572285	QBML-5/32T-U	10
1/4	0.197	11.2	3.3	17.6	7.0	0.176	573063	QBML-1/4T-U	10



1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch

Technical data

Push-in T-fitting QBMT

Male thread
with external hex



Dimensions and ordering data												
Connection	Nominal size	Tubing O.D.	D5 Ø	H1	H2	H3	L1	≡	Weight/piece [oz]	Part No.	Type	PU ¹⁾
D1	[inch]	D2										
UNF thread												
10-32	0.098	1/8	7.6	15.3	3.6	11.7	29.0	5/16	0.071	533304	QBMT-10-32-UNF-1/8-U	10
	0.098	5/32	8.7	15.9	3.6	12.3	30.2	5/16	0.088	572289	QBMT-10-32-UNF-5/32-U	10
	0.098	1/4	11.3	17.2	3.6	13.6	32.2	5/16	0.353	573067	QBMT-10-32-UNF-1/4-U	10
NPT thread												
1/8	0.098	1/8	7.6	15.8	8.5	11.7	29.0	7/16	0.176	533308	QBMT-1/8-1/8-U	10
	0.098	1/4	11.3	17.7	8.5	13.6	32.2	7/16	0.423	572291	QBMT-1/8-1/4-U	10
1/4	0.138	1/8	7.6	18.3	10.5	12.5	29.0	9/16	0.564	573068	QBMT-1/4-1/4-U	10


1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch


Technical data

FESTO

Push-in T-connector QBMT-...T



Reducing



Dimensions and ordering data

Tubing O.D.	Nominal size	Tubing O.D.	D4 Ø	D5 Ø	D6 Ø	H1	L1	L2	Weight/piece [oz]	Part No.	Type	PU ¹⁾
D1	[inch]	D2										
1/8	0.094	–	–	7.5	3.2	13.5	27.0	10.8	0.106	572293	QBMT-1/8T-U	10
5/32	0.118	–	–	8.4	3.2	14.5	29.0	11.6	0.141	572294	QBMT-5/32T-U	10
1/4	0.197	–	–	11.2	3.3	17.6	35.2	14.0	0.212	573069	QBMT-1/4T-U	10
Reducing												
5/32	0.094	1/8	8.4	8.4	3.2	14.4	14.5	5.8	0.141	572292	QBMT-5/32T-1/8-U	10
1/4	0.118	5/32	11.2	11.2	3.3	17.6	17.6	7.0	0.176	573070	QBMT-1/4T-5/32-U	10


1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch

Technical data

Push-in T-fitting QBMTL

Male thread
with external hex



Dimensions and ordering data													
Connection	Nominal size	Tubing O.D.	D5 Ø	H1	H2	H3	H4	L1	⌀	Weight/piece [oz]	Part No.	Type	PU ¹⁾
D1	[inch]	D2											
UNF thread													
10-32	0.098	1/8	7.6	28.9	3.6	15.3	11.7	13.6	5/16	0.071	572295	QBMTL-10-32-UNF-1/8-U	10
	0.098	5/32	8.7	30.4	3.6	15.9	12.3	14.5	5/16	0.176	572296	QBMTL-10-32-UNF-5/32-U	10
	0.098	1/4	11.2	35.0	3.6	17.1	13.5	17.9	5/16	0.353	573071	QBMTL-10-32-UNF-1/4-U	10
NPT thread													
1/8	0.098	1/8	7.6	29.4	8.5	15.8	11.7	13.6	7/16	0.176	572297	QBMTL-1/8-1/8-U	10
	0.098	1/4	11.2	35.5	8.5	17.6	13.5	17.9	7/16	0.423	572298	QBMTL-1/8-1/4-U	10
1/4	0.118	1/8	7.6	31.9	10.5	18.3	12.5	13.6	9/16	0.564	573072	QBMTL-1/4-1/8-U	10



1) Packaging unit

Push-in fittings QBM, Quick Basic, mini, inch

Technical data

FESTO

Push-in Y-connector QBM Y-...T



Reducing

Dimensions and ordering data											
Tubing O.D.	Nominal size	Tubing O.D.	D4	D5	D6	H1	L1	Weight/piece	Part No.	Type	PU ¹⁾
D1	[inch]	D2	Ø	Ø	Ø			[oz]			
1/8	0.094	–	–	7.6	3.2	7.6	26.8	0.141	572299	QBM Y-1/8T-U	10
5/32	0.118	–	–	8.7	3.2	8.7	28.0	0.106	572300	QBM Y-5/32T-U	10
1/4	0.197	–	–	11.3	3.2	11.3	32.6	0.176	573073	QBM Y-1/4T-U	10
Reducing											
1/8	0.094	5/32	7.6	8.7	3.2	7.6	27.5	0.141	572301	QBM Y-5/32T-1/8-U	10
5/32	0.118	1/4	8.7	11.3	3.2	8.7	29.8	0.176	573074	QBM Y-1/4T-5/32-U	10

1) Packaging unit

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788
Phone: 1.631.435.0800; Fax: 1.631.435.8026;
Email: info@festo-usa.com www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4
Phone: 1.905.624.9000; Fax: 1.905.624.9001;
Email: festo.canada@ca.festo.com www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México
Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;
Email: festo.mexico@mx.festo.com www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com