

Electrical connection technology, for fieldbus connection

FESTO


Technical data – SIE-GA

- Plug pin adapter for fieldbus connection
- 4-pin
- Plug, straight



General technical data	
Type	SIE-GA
Type of mounting	Via union nut
Max. tightening torque for locking [Nm]	0.6
Mounting position	Any
Operating voltage range [V]	≤250 DC, ≤250 AC
Surge capacity [kV]	2.5
Acceptable current load at 40 °C [A]	4
Protection class to EN 60529	IP67
Based on standard	EN 61076-2-101 EN 61984
Material of contacts	Brass
Material of union nut	Nickel-plated and gold-plated brass
Note on materials	Conforms to RoHS

Operating and enviromental conditions	
Ambient temperature [°C]	-25 ... +85
CE mark (see declaration of conformity)	In accordance with EU-Low Voltage Directive
Degree of contamination	3

Ordering data				
	Electrical connection	Product weight [g]	Type	Part No.
	Plug, straight, 4-pin, M12x1, design A	23.5	SIE-GA	18780

Dimensions		Download CAD data → www.festo.com
