



Adapter

Type AD-...

With NPT Thread Male and ISO Thread Female



SW = wrench size (mm)




Order Number		Connection		Material	Weight lb / kg	Dimensions			
Part No.	Type	D ₁ Male	D ₂ Female			B in / mm	L in / mm	NW in / mm	SW in / mm
9624	AD-1/8 NPT-G 1/8 I	1/8 NPT	G 1/8 ISO	Zinc plated steel with sealing ring	0.020 / 0.009	0.35 / 9	0.79 / 20	0.23 / 6	1/2 / 12.7
9625	AD-1/4 NPT-G 1/4 I	1/4 NPT	G 1/4 ISO		0.048 / 0.022	0.5 / 13	1.05 / 27	0.3 / 8	11/16 / 17
9626	AD-3/8 NPT-G 3/8 I	3/8 NPT	G 3/8 ISO		0.050 / 0.023	0.56 / 14.5	1.2 / 30.5	0.45 / 11.5	3/4 / 19
9627	AD-1/2 NPT-G 1/2 I	1/2 NPT	G 1/2 ISO		0.100 / 0.047	0.7 / 12.5	1.44 / 36.5	0.56 / 14.3	15/16 / 24
546551	AD-3/4 NPT-G 3/4 I	3/4 NPT	G 3/4 ISO		0.33 / 0.150	0.7 / 18	1.68 / 43	0.75 / 19	17/16 / 36
546547	AD-1 NPT-G 1 I	1 NPT	G 1 ISO		-	-	-	-	-


Adapter

Type AD-...

With ISO Thread Male and NPT Thread Female



SW = wrench size (mm)




Order Number		Connection		Material	Weight lb / kg	Dimensions			
Part No.	Type	D ₁ Male	D ₂ Female			B in / mm	L in / mm	NW in / mm	SW in / mm
9395	AD-G 1/8-1/8 NPT I	G 1/8 ISO	1/8 NPT	Zinc plated steel with sealing ring	0.022 / 0.010	0.19 / 5	0.81 / 20.5	0.23 / 6	1/2 / 12.7
9396	AD-G 1/4-1/4 NPT I	G 1/4 ISO	1/4 NPT		0.052 / 0.024	0.25 / 6.5	1.04 / 26.5	0.3 / 8	11/16 / 17
9397	AD-G 3/8-3/8 NPT I	G 3/8 ISO	3/8 NPT		0.052 / 0.024	0.33 / 8.5	1.10 / 28	0.45 / 11.5	3/4 / 19
9398	AD-G 1/2-1/2 NPT I	G 1/2 ISO	1/2 NPT		0.108 / 0.049	0.45 / 11.5	1.41 / 36	0.56 / 14.5	15/16 / 24
546550	AD-G 3/4-3/4 NPT I	G 3/4 ISO	3/4 NPT		0.310 / 0.140	0.55 / 14	1.48 / 38	0.7 / 12.5	17/16 / 36
546546	AD-G 1-1 NPT I	G 1 ISO	1 NPT		0.420 / 0.190	0.63 / 16	1.71 / 44	0.95 / 24	15/8 / 41

Hex Nipple

Type E-...

Adapter Nipple
With ISO and NPT Thread



SW = wrench size (mm)



Order Number		Connection		Material	Weight lb / kg	Dimensions			
Part No.	Type	D ₁ Male	D ₂ Male			B in / mm	L in / mm	NW in / mm	SW in / mm
9630	E-G 1/8-1/8 NPT	G 1/8 ISO	1/8 NPT	Zinc plated steel with sealing ring	0.022 / 0.010	0.19 / 5	0.81 / 20.5	0.23 / 6	1/2 / 12.7
9631	E-G 1/4-1/4 NPT	G 1/4 ISO	1/4 NPT		0.044 / 0.020	0.25 / 6.5	1.03 / 26.5	0.3 / 7	11/16 / 17
9632	E-G 3/8-3/8 NPT	G 3/8 ISO	3/8 NPT		0.052 / 0.024	0.33 / 8.5	1.18 / 30	0.45 / 11.5	3/4 / 19
9633	E-G 1/2-1/2 NPT	G 1/2 ISO	1/2 NPT		0.103 / 0.047	0.45 / 11.5	1.42 / 36.5	0.56 / 14.5	15/16 / 24
546549	E-G 3/4-3/4 NPT	G 3/4 ISO	3/4 NPT		1.664 / 0.755	0.55 / 14	1.85 / 47	0.7 / 17.5	17/16 / 36

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change