


Connecting cables NEBV, for valves

Technical data

Connecting cable NEBV-M8W4L

- For CPE10 and CPE14
- With round plug
- Cable lengths 2.5 to 10 m



General technical data		
Type	NEBV-M8W4L-...-LE2	NEBV-M8W4L-...-M8G3
Electrical connection	Angled socket, M8x1, 4-pin	Angled socket, M8x1, 4-pin
	Cable, 2-wire	Straight plug, M8x1, 3-pin
Operating voltage range [V DC]	20.4 ... 26.4	
Acceptable current load [A] at 40 °C	3	
Switching status display	Yellow LED	
Tightening torque [Nm]	0.3	
Cable composition [mm ²]	2x0.25	
Cable diameter [mm]	3.4	
Wire ends	Wire end sleeve	-
Conforms to	EN 61076-2-101, ISO 20401	
Cable characteristics	Suitable for use with energy chains	
Protection class to EN 60529	IP65 and IP67 (assembled)	

Materials	
Housing	TPE-U (PU)
Pin contacts	Gold-plated brass
Insulating sheath	PVC
Cable sheath	Polyurethane
Note on materials	RoHS-compliant

Operating and environmental conditions		
Ambient temperature [°C]	-10 ... +50	
Min. cable bending radius [mm]	35	

Circuitry (socket/plug view)				
Socket	Pin	Wire colour	Pin	Plug
NEBV-M8W4L-...-M8G3				
	1	-	1	
	2	-	-	
	3	Brown	3	
	4	Blue	4	
NEBV-M8W4L-...-LE2				
	1	-	-	
	2	-	-	
	3	Black	-	
	4	Black	-	

Connecting cables NEBV, for valves

Technical data

Dimensions Download CAD Data → www.festo.com/us/cad

NEBV-M8W4L-...-LE2

1 Open cable end, 2-wire
 2 Angled socket, 4-pin, transparent housing, with LED
 3 Inscription label holder

NEBV-M8W4L-...-M8G3

2 Angled socket, 4-pin, transparent housing, with LED
 3 Inscription label holder
 4 Straight plug, 3-pin

	B1	D1	D2	D3	D4	D5	L1	L2	L3
NEBV-M8W4L-E-2.5-LE2	17	3.4	9	M8x1	-	-	2,500	50	26.9
5,000									
10,000									
NEBV-M8W4L-E-2.5-M8G3	17	3.3	9	M8x1	M8x1	9.6	2,500	41.1	26.9
5,000									
10,000									

Ordering data					
	Description	Product weight [g]	Cable length [m]	Part No.	Type
	Angled socket, M8x1, 4-pin; cable, 2-wire	45	2.5	562471	NEBV-M8W4L-E-2.5-LE2
		85	5	562472	NEBV-M8W4L-E-5-LE2
		165	10	562473	NEBV-M8W4L-E-10-LE2
	Angled socket, M8x1, 4-pin; straight plug, M8x1, 3-pin	50	2.5	562468	NEBV-M8W4L-E-2.5-M8G3
		90	5	562469	NEBV-M8W4L-E-5-M8G3
		170	10	562470	NEBV-M8W4L-E-10-M8G3

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com