Air guns





Low consumption air guns LSP-1/4-D

Technical data

FESTO



Operating pressure
0 ... 10 bar



- Precise, infinitely variable, lever operated flow metering
- Sturdy aluminium design
- Interchangeable nozzles

General technical data

| General technical uata | | | | | | |
|--------------------------------|----------|--|--|--|--|--|
| Exhaust function | | Metered blowing | | | | |
| Pneumatic connection | | Female thread G1⁄4 | | | | |
| Operating medium | | Compressed air in accordance with ISO 8573-1:2010 [7:-:-] | | | | |
| Note on operating/pilot medium | | Operation with lubricated medium possible (in which case lubricated operation will always be required) | | | | |
| Operating pressure | [bar] | 010 | | | | |
| Standard nominal flow rate | [l/min] | 120 at 6 bar | | | | |
| Noise level | [dB (A)] | 90 at 6 bar | | | | |
| Ambient temperature | [°C] | -10 +50 | | | | |
| Weight | [g] | 240 | | | | |

Note: This product conforms to ISO 1179-1 and to ISO 228-1

| Materials | |
|-------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Note on materials | RoHS-compliant |



Note: This product conforms to ISO 1179-1 and to ISO 228-1

| Ordering data | | |
|----------------------|----------|-----------|
| Pneumatic connection | Part No. | Туре |
| G1⁄4 | 35528 | LSP-1/4-D |

Low consumption air guns LSP-1/4-C

- Precise, infinitely variable, lever operated flow metering
- Interchangeable nozzles





Download CAD data → www.festo.com

| General technical data | | |
|--------------------------------|----------|--|
| Exhaust function | | Metered blowing |
| Pneumatic connection | | Female thread G1/4 |
| Operating pressure | [bar] | 010 |
| Operating medium | | Compressed air in accordance with ISO 8573-1:2010 [7:-:-] |
| Note on operating/pilot medium | | Operation with lubricated medium possible (in which case lubricated operation will always be required) |
| Standard nominal flow rate | [l/min] | 120 at 6 bar |
| Noise level | [dB (A)] | 90 at 6 bar |
| Ambient temperature | [°C] | -10 +50 |
| Weight | [g] | 125 |

Note: This product conforms to ISO 1179-1 and to ISO 228-1





Note: This product conforms to ISO 1179-1 and to ISO 228-1

1.5

| Ordering data | | |
|----------------------|----------|-----------|
| Pneumatic connection | Part No. | Туре |
| G1⁄4 | 184318 | LSP-1/4-C |

Air guns Accessories

Air gun nozzle LPZ-SD

with safety shield

- Accurate, high power air jet with protective air shield for chips and dust
- Low noise level





| Operating and environmental conditions | | | | |
|--|---------|---------|--|--|
| Ambient temperature | [°C] | -10 +50 | | |
| Noise level | [dB(A)] | 80 | | |
| Noise level | [dB(A)] | 80 | | |

| Materials | |
|-------------------|----------------|
| Air gun nozzle | Aluminium |
| Note on materials | RoHS-compliant |
| | |

Dimensions and ordering dat

| Dimensions and ordering data | | | | | | | |
|------------------------------|----|-----|----|----|------|----------|--------|
| Pneumatic connection | D2 | D3 | L1 | L2 | =© 1 | Part No. | Туре |
| D1 | Ø | Ø | | | | | |
| Male thread M12x1.25 | 7 | 0.8 | 26 | 10 | 14 | 184321 | LPZ-SD |

Air gun nozzle LPZ-LD

with noise reduction

- Powerful, focused air jet
- For blowing out, drying and cooling large surfaces

• Low noise level

4



| Operating and environmental conditions | | | | | |
|--|----------------------------------|--|--|--|--|
| Ambient temperature | [°C] | -10 +50 | | | |
| | | | | | |
| Materials | | | | | |
| Air gun nozzle | | Chrome plated die-cast zinc, aluminium | | | |
| Note on materials | Note on materials RoHS-compliant | | | | |

Dimensions and ordering data

| Dimensions and ordering data | | | | | | |
|------------------------------|------|----|----|------|----------|--------|
| Pneumatic connection | D2 | L1 | L2 | =© 1 | Part No. | Туре |
| D1 | Ø | | | | | |
| Male thread M12x1.25 | 17.6 | 41 | 8 | 17 | 184322 | LPZ-LD |

→ Internet: www.festo.com/catalogue/...

Subject to change - 2015/02

Air guns Accessories

Air gun nozzle LPZ-RG-150-B

with straight tube

• Accurate, high power air jet for difficult to access locations





Operating and environmental conditions

| Ambient temperature | [°C] | -10 +50 | | | |
|---------------------|---------|---------|--|--|--|
| Noise level | [dB(A)] | 90 | | | |
| | | | | | |

| Materials | |
|-------------------|---------------------|
| Air gun nozzle | Nickel-plated brass |
| Note on materials | RoHS-compliant |
| | |

| Dimensions and ordering data | | | | | | | | | |
|------------------------------|----|----|----|-----|----|----|------|----------|--------------|
| Pneumatic connection | D1 | D3 | D4 | L1 | L2 | L3 | =© 1 | Part No. | Туре |
| D2 | Ø | Ø | Ø | | | | | | |
| Male thread M12x1.25 | 5 | 4 | 3 | 173 | 30 | 8 | 17 | 565317 | LPZ-RG-150-B |

Air gun nozzle LPZ-RB-150-B

with elbow tube

- Accurate, high power air jet for difficult to access locations
- 360° rotatable



Operating and environmental conditions

| Ambient temperature | [°C] | -10 +50 | | | | | |
|---------------------|---------|---------|--|--|--|--|--|
| Noise level | [dB(A)] | 90 | | | | | |
| | | | | | | | |

| Materials | |
|-------------------|---------------------|
| Air gun nozzle | Nickel-plated brass |
| Note on materials | RoHS-compliant |

| Dimensions and ordering data | | | | | | | | | |
|------------------------------|----|----|----|-----|----|----|------|----------|--------------|
| Pneumatic connection | D1 | D3 | D4 | L1 | L2 | L3 | =© 1 | Part No. | Туре |
| D2 | Ø | Ø | Ø | | | | | | |
| Male thread M12x1.25 | 5 | 4 | 3 | 168 | 30 | 8 | 17 | 565316 | LPZ-RB-150-B |

Air guns Accessories

