## Type codes

001	Series	- 1	002	Use	
KASI	Connecting cable for AS-Interface		ADR	Addressing cable	

## Data sheet

## Addressing cable KASI-ADR

- T-distributor
- Pre-assembled at three ends
- For connecting the AS-Interface addressing device to any AS-Interface slaves
- Cable length 2.5 m



General technical data	
Distributor type	2 to 1
Protocol	AS-Interface
Design	T-distributor with cable at both ends
Cable designation	Without inscription label holder

Technical data – Electrical connection 1			
Function	Field device side		
Connection type	Socket		
Cable outlet	Angled		
Design	Rectangular		
Connection technology	AS-Interface		
Number of pins/wires	2		
Assigned pins/wires	2		
Type of mounting	Plug-in		

Technical data – Electrical connection 2				
Function	Field device side			
Connection type	Socket			
Cable outlet	Straight			
Design	Round			
Connection technology	M12x1, A-coded to EN 61076-2-101			
Number of pins/wires	4			
Assigned pins/wires	2			
Type of mounting	Plug-in			

Technical data – Electrical connection 3	nnical data – Electrical connection 3			
Function	Controller side			
Connection type	Plug			
Cable outlet	Angled			
Design	Round			
Connection technology	M12x1, A-coded to EN 61076-2-101			
Number of pins/wires	4			
Assigned pins/wires	2			
Type of mounting	Plug-in			


Technical data – Electrics		
Operating voltage range	[V DC]	048
	[V AC]	048
Surge resistance	[kV]	0.5
Acceptable current load at 40°C	[A]	3
Pollution degree		2
Additional functions Con		Connecting the programming device to an AS-Interface component via AS-i flat cable.


## Data sheet

Technical data – Cable		
Cable length 1	[m]	2.4
Cable length 2	[m]	0.1
Cable composition	[mm <sup>2</sup> ]	2x1.5
Nominal conductor cross section	[mm <sup>2</sup> ]	1.5
Cable characteristic		Standard
Cable test conditions		Test conditions on request

Materials		
Housing colour	Black	
Cable sheath	Rubber compound	
Cable sheath colour	Yellow	
Note on materials	RoHS-compliant	

Operating and environmental conditions		
Ambient temperature [°C]	-40 +85	
Ambient temperature with flexi- [°C]	-25 +80	
ble cable installation		
Degree of protection	IP20	
Note on degree of protection	In assembled state	





Ordering data			
	Cable length	Part no.	Туре
	[m]		
Socket M12x1, 4-pin – AS-Interface socket, 2-pin – plug M12x1, 4-pin	2.5	18960	KASI-ADR