Data sheet

Elbow fitting LJK



Operating pressure -0.95 ... 8 bar

• Rerouting the air connection • Swivel joint rotatable 360°

Note -

For suction cup VAS/VASB

• For decoupling from mounting thread



General technical data

General technical data						
Size		M5	G1/8	G1/4		
Design		Swivel fitting with female thread				
Operating medium		Atmospheric air based on ISO 8573-1:2010 [7:-:-]				
Mounting position		Any				
Type of mounting		Option for mounting the lateral air connection	nection on the male thread of the hollow bolt			
Vacuum connection		M5	G1/8	G1/4		
Operating pressure [ba	ar]	-0.95 8				

Environmental conditions					
Size		M5	G1/8	G1/4	
Swivel fitting		Die-cast zinc			
Seals		Nitrile rubber and steel/nitrile rubber			
Note on materials		Free of copper, PTFE and silicone			
Ambient temperature	[°C]	-10 +60			
Corrosion resistance class	CRC ¹⁾	2			

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Dimensions





[1] Air connection (vacuum)

[2] Mounting thread

Vacuum connection	В	D	Н	H1	H2	L	L1	-C
M5	10	M5	20.3	3.8	7.5	17.5	12.5	8
G1/8	16	G1/8	30	5	10.6	28	20	13
G1/4	20	G1/4	39	8	13.5	36	26.5	17

Ordering data

Part no.	Туре		
151 783	LJK-M5-I/I		
151 784	LJK-1/8-I/I		
151 785	LJK-1/4-I/I		
	151 783 151 784		

I