

Indicator insert MCL-24DC/AC

Part number: 10000

FESTO



Data sheet

Feature	Value
Product weight	12 g
Electrical connection	Type A Plugs To DIN EN 175301-803
Nominal operating voltage DC	24 V
Nominal operating voltage AC	24 V
Mains frequency	0 Hz...60 Hz
Permissible voltage fluctuations	+/- 15%
Degree of protection	IP65 To IEC 60529
Ambient temperature	-20 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA6 reinforced