

Indicator insert MFL-230AC

Part number: 10005

FESTO



Data sheet

Feature	Value
Product weight	14 g
Electrical connection	Type B To industry standard (11 mm)
Nominal operating voltage AC	230 V
Mains frequency	50 Hz...60 Hz
Permissible voltage fluctuations	-20 % / +15 %
Degree of protection	IP65 To IEC 60529
Ambient temperature	-20 °C...60 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA6 reinforced