


Axial kit EAMM-A-R27-55A

Part number: 1133400

FESTO



Data sheet

Feature	Value
Nominal length	26 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	0.445 kgmm ²
Transmittable torque	2 Nm
Product weight	170 g
Interface code, actuator	R27
Interface code, motor in	55A
Note on materials	RoHS-compliant