


Axial kit EAMM-A-R38-87A

Part number: 1133404

FESTO



Data sheet

| Feature | Value |
|--------------------------|-----------------------|
| Nominal length | 38 mm |
| Mounting position | optional |
| Max. rotational speed | 8000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95% |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C...60 °C |
| Mass moment of inertia | 3.2 kgmm ² |
| Transmittable torque | 4.4 Nm |
| Product weight | 530 g |
| Interface code, actuator | R38 |
| Interface code, motor in | 87A |
| Note on materials | RoHS-compliant |