


round cylinder EG-25- -

Part number: 11649

FESTO

With spring return



Exemplary representation

Data sheet

| Feature | Value |
|--|---|
| Stroke | 1 ... 80 mm |
| Piston diameter | 25 mm |
| Cushioning | No cushioning |
| Position detection | No |
| Variants | Single-ended piston rod |
| Operating pressure | 1 ... 8 bar |
| Mode of operation | single-acting pushing action |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Ambient temperature | -20 ... 80 °C |
| Theoretical force at 6 bar, advance stroke | 215 N |
| Pneumatic connection | G1/8 |