

# Barbed elbow fitting LCN-1/8-PK-6

Part number: 11957

FESTO



## Data sheet

| Feature                                       | Value  |
|---|--|
| Nominal size                                  | 4.9 mm   |
| Type of seal on screwed plug                  | Sealing ring   |
| Operating pressure complete temperature range | -0.95 bar...10 bar   |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:...]  |
| Note on operating and pilot medium            | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                        | VDMA24364-B1/B2-L  |
| Ambient temperature                           | 0 °C...60 °C   |
| Pneumatic connection, port 1                  | Male thread G1/8   |
| Pneumatic connection, port 2                  | For tubing outside diameter of 8 mm  |
| Note on materials                             | RoHS-compliant   |
| Material housing                              | Aluminium<br>Die-cast zinc   |