

Parallel kit EAMM-U-145-S95-140A-288

Part number: 1220582

FESTO



Data sheet

| Feature | Value |
|---------------------------------------|------------------------|
| Size | 145 |
| Mounting position | optional |
| Gear unit ratio | 1:1 |
| Max. rotational speed | 4000 rpm |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95% |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C...60 °C |
| Mass moment of inertia | 2270 kgmm ² |
| Frictional torque independent of load | 2 Nm |
| Transmittable torque | 50 Nm |
| Product weight | 14850 g |
| Interface code, actuator | S95 |
| Interface code, motor in | 140A |
| Note on materials | RoHS-compliant |