


adapter plate

VABA-S6-7-S2-3-P-G1

Part number: 1302079
Product to be discontinued

FESTO

Type to be discontinued. Available until 2026. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|---|---|
| Width | 60 mm |
| Assembly position | Any |
| Max. number of solenoid coils | 26 |
| Operating pressure | -0.9 ... 10 bar |
| Nominal operating voltage DC | 24 V |
| Permissible voltage fluctuation | +/- 10 % |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Protection class | IP65 NEMA 4 |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 2,600 g |
| Auxiliary pilot air port 12 | G1/8 |
| Auxiliary pilot air port 14 | G1/8 |
| Pneumatic connection, port 1 | G1 |
| Pneumatic connection, port 3 | G1 |
| Pneumatic connection, port 5 | G1 |
| Materials note | Conforms to RoHS |
| Material seals | NBR |
| Material plate | Wrought Aluminium alloy |
| Material screws | Steel Galvanised |