


push-in T-fitting QSMT-B-M5-3-20

Part number: 132113
Product to be discontinued

FESTO

360° orientable, male thread with external hexagon.
Type to be discontinued. Available until 2018. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|---|---|
| Size | Mini |
| Nominal size | 1.6 mm |
| Type of seal on screw-in stud | Sealing ring |
| Assembly position | Any |
| Container size | 20 |
| Design structure | Push/pull principle |
| Operating pressure complete temperature range | -0.95 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:::] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 |
| Ambient temperature | -10 ... 60 °C |
| Authorisation | Germanischer Lloyd |
| Max. tightening torque | 1.5 Nm |
| Product weight | 3.3 g |
| Number of outputs | 2 |
| Number of supply lines | 1 |
| Pneumatic connection, port 1 | Male thread M5 |
| Pneumatic connection, port 2 | for tubing, 3mm outside diameter |
| Colour of release ring | blue |
| Materials note | Conforms to RoHS |
| Materials information, housing | PBT |
| Release ring material data | POM |
| Materials information for tubing seal | NBR |
| Hose clamping segment material data | High alloy steel, non-corrosive |