

# Push-in L-fitting NPQP-L-R14-Q6-FD-P10

Part number: 133054

FESTO



## Data sheet

| Feature                                  | Value                                    |
|--|--|
| Size                                     | Standard                                 |
| Nominal size                             | 3.3 mm                                   |
| Design                                   | L-shape<br>Push-pull principle           |
| Size of pack                             | 10                                       |
| Temperature-dependent operating pressure | -0.95 bar...10 bar                       |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:~:] |
| Note on operating and pilot medium       | Lubricated operation possible            |
| Corrosion resistance class CRC           | 4 - Very high corrosion stress           |
| LABS (PWIS) conformity                   | VDMA24364 zone III                       |
| Suitable for use with food               | See supplementary material information   |
| Ambient temperature                      | -20 °C...60 °C                           |
| Product weight                           | 5.5 g                                    |
| Type of mounting                         | External hexagon, size 14 mm             |
| Pneumatic connection, port 1             | Male thread R1/4                         |
| Pneumatic connection, port 2             | For tubing outside diameter of 6 mm      |
| Note on materials                        | RoHS-compliant                           |
| Material housing                         | PP                                       |
| Material tubing clamp component          | High-alloy stainless steel               |