

Push-in L-fitting NPQP-LQ-R14-Q4-FD-P10

Part number: 133062

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | Standard |
| Nominal size | 2 mm |
| Design | T-shape, additional push-in connector, lengthwise Push-pull principle |
| Size of pack | 10 |
| Temperature-dependent operating pressure | -0.95 bar...10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:~:] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 4 - Very high corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Suitable for use with food | See supplementary material information |
| Ambient temperature | -20 °C...60 °C |
| Product weight | 6.5 g |
| Type of mounting | External hexagon, size 14 mm |
| Pneumatic connection, port 1 | Male thread R1/4 |
| Pneumatic connection, port 2 | For tubing outside diameter of 4 mm |
| Note on materials | RoHS-compliant |
| Material housing | PP |
| Material tubing clamp component | High-alloy stainless steel |