

Clamping sleeve EAMH-145-25-C34-P

Part number: 1354110

FESTO



Data sheet

| Feature | Value |
|------------------------|------------------------|
| Size | 145 |
| Mounting position | optional |
| Max. rotational speed | 4000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -10 °C...60 °C |
| Mass moment of inertia | 32.1 kgmm ² |
| Product weight | 217 g |
| Note on materials | RoHS-compliant |