

# Coupling EAMC-67-62-24-32

Part number: 1485796

FESTO



## Data sheet

Feature	Value
Mounting diameter 1	24 mm
Mounting diameter 2	32 mm
Size	67
Nominal length	62 mm
Mounting position	optional
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	280 kgmm <sup>2</sup>
Transmittable torque	143 Nm
Product weight	428 g
Note on materials	RoHS-compliant