

Rod clevis SG-M27X2-B

Part number: 14987

FESTO



Data sheet

| Feature | Value |
|--|---|
| Size | M27x2 |
| Conforms to standard | ISO 8140 |
| Threaded connection | Female thread M27x2 |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical plug connectors and coils |
| Ambient temperature | -40 °C...150 °C |
| Product weight | 2135 g |
| Note on materials | RoHS-compliant |
| Material bolt | Steel Galvanised |
| Material clevis | Steel Galvanised |
| Material nut | Steel Galvanised |