

Profile strip SLZS-25- -

Part number: 150917

FESTO



Data sheet

| Feature | Value |
|--------------------------------|--|
| Design | T-slot for proximity switch Sensor rail |
| Max. profile length | 2800 mm |
| Mounting position | optional |
| For piston diameter | Ø20 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -20 °C...60 °C |
| Type of mounting | Via through-hole and screw |
| Material profile | Wrought aluminium alloy Anodised |
| Note on materials | RoHS-compliant |
| Material screws | High-alloy steel |